



CODE: ST03-026000005-001PL









STERYLIS VS is a line of devices with an ozone generator with increased power, additionally using the UV-C technology in the disinfection process and two-stage air filtration.

Maximum recommended cubic capacity rooms for **UV-C** disinfection

Maximum recommended cubic capacity rooms for **O**<sub>3</sub> sterylization

100 m<sup>3</sup>
450 m<sup>3</sup>

## **WORK MODES:**



Filtration



**Disinfection UV-C** 



UV-C disinfection - silent mode



Sterilization
O3 + UV-C (Auto)




## **TECHNICAL SPECIFICATIONS:**


STANDARD MODE – UV-C DISINFECTION	
The maximum dose of UV-C radiation	112 J/m²
Fan performance UV-C disinfection mode	220 m³/h
Noise level – disinfection mode UV-C	50 dB(A)
SILENT MODE – UV-C DISINFECTION	
The maximum dose of UV-C radiation	149 J/m²
Noise level – disinfection mode UV-C (silent)	45 dB(A)
MODE – STERILIZATION O3 + UV-C	
Maximum cubic capacity of the sterilized room (to achleve 5 ppm O <sub>3</sub> )	450 m³
Ozone generator capacity	30 000 mg/h
Fan capacity Sterilization mode O3+UV-C	265 m³/h
Noise level – sterilization mode O3+UV-C	53 dB(A)
FILTRATION MODE	
Fan capacity in filter mode	220 m³/h
Noise level – filtering mode	50 dB(A)
UV lamp	YES





CODE: ST03-026000005-001PL





Type lamps UV	UV-C sterilization λ= 253,7 nm	
Total electrical power of UV-C sources	54 W	
Durability of UV lamps	9000 h	
Total radiant power of UV-C sources	14,4 W	
Ozone generator	YES	
Ozone concentration sensor	YES	
Ozone destructor	YES	
Air filtering	2-stage	
Fan type	Radial	
Fan engine	enclosed	
Туре	flowtype	
Controller	YES	
Automatic mode of operation	YES (control of sterilization time according to actual ozone concentration readings)	
Self-diagnosis	YES	
Working time counter	YES (signaling the replacement of filters and UV radiators	
Power supply	230 V (AC), 50 Hz	
Rated current	2,0 A	
Rated power	470 W	
Power cable length	3 m / 10 m*	
Dimensions (H x W x D)	710 x 360 x 260	
Net weight	18 kg	
Type of housing	metal, powder-coated	
Transport wheels/handles	Handle/transport wheels*	
Additional functions	signaling safe and excessive ozone levels, detachable power cord	

<sup>\* -</sup> option available after consultation with the sales department

Due to the continuous development of our products, we reserve the right to make changes to the design of the devices and to update their parameters.

Revision Date: 12.04.2021

